



# Allowable overhang Note



**Horizontal installation** (Unit: mm)

**Wall installation** (Unit: mm)

|             | A    | B    | C    |
|-------------|------|------|------|
| <b>3kg</b>  | 5767 | 1353 | 1247 |
| <b>8kg</b>  | 1839 | 399  | 458  |
| <b>14kg</b> | 829  | 154  | 254  |

|             | A    | B    | C    |
|-------------|------|------|------|
| <b>3kg</b>  | 1324 | 1354 | 5588 |
| <b>8kg</b>  | 474  | 399  | 1658 |
| <b>14kg</b> | 255  | 151  | 643  |

Note. Distance from center of slider upper surface to carrier center-of-gravity at a guide service life of 10,000km (This does not warrant the service life of the product.). (Service life is calculated for 600mm stroke models.)